



Knapstein

HELLI-3

Oberfläche

- nickel
- black
- bronze

Struktur

- nickel
- black
- bronze

Technical details

Country of Manufacture	 Germany
Manufacturer	Knapstein
Year of design	2024
material	Acryl, Metall
height adjustment	height adjustable
dimming	gesture control
Wattage	6x8 W
LED #	inclusive
Colour Rendering Index	>90
Luminous flux in lm	6420
Color temperature in Kelvin	2.700 extra warm white
protection	IP20
Scope of delivery	LED
canopy	120x4,5 cm
bulb exchange	at the manufacturer / at the factory
total height	70 - 170 cm

Description

The Knapstein HELLI-3 LED pendant lamp has three cylindrical lamp bodies with freely combinable structures on the underside. The lenses of the lower diffusers are reversible, making it easy to choose between a lens for a focussed lighting effect and a disc for a diffuse lighting effect. To do this, unscrew the lower luminaire ring and replace the enclosed glass in the desired position (lens/disc). The aforementioned screw ring (structure) is available in 3 different colours. A swiping hand movement in the sensor area switches the corresponding light source on or off. To dim the light, the hand is held in front of the respective sensor until the desired light intensity is reached. Thanks to the integrated memory function, the last settings are saved and are immediately available again the next time the light is switched on. The uplight and downlight can be switched and dimmed separately using gesture control. Thanks to individual lift suspensions, the height of the three lamp bodies can be infinitely adjusted from approx. 70 cm - 170 cm at any time by simply pulling or lifting - even on sloping ceilings. The Knapstein HELLI-3 has a synchronisation function that enables the light intensity to be adjusted evenly across all three light sources. The rectangular ceiling canopy of the Knapstein HELLI-3 LED pendant lamp has a magnetic holder, so no external screw connections are visible. This pendant lamp is available in several surfaces and freely combinable external structures on the underside.